


**Re-Bo**
**Stainless steel circular saw blade coarse, Ø×thickness: 315X3mm**


## Order data

Order number	177540 315X3
GTIN	4045197245441
Item class	17B

## Description

### Version:

Precision toothing and very fine ground side faces. **Rake angle especially for stainless steels.**

**Nitrided surface:** hard, durable protection against edge build-up.

### Application:

**Pitch t:** (tooth form)

- **3 mm (BW)** – For thin pipes, profiles, sheet metal with 1 – 2 mm wall thickness.
- **4 mm (BW)** – For pipes, profiles, sheet metal with 1.5 – 4 mm wall thickness.
- **6 mm (HZ)** – For pipes, profiles and solid material above 4 mm wall thickness or cross-section up to a maximum of. 50 mm.
- **8 mm (HZ)** – For solid material above 50 mm.

### Suitable for:

**EISELE** and **TRENNJAEGER** cold circular saws.

### Note:

- **For optimum performance and service life: Use cooling lubricant concentrate No. 084260.**
- **The concentricity and axial run-out values are considerably better than the figures according to DIN 1840, in some cases by up to 50 %.**

## Technical description

Bore Ø	40 mm
Ø	315 mm
Pitch t	8 mm
Thickness	3 mm
No. of teeth Z	120
Number of drive holes	2; 4
Drive hole pitch circle	55; 64 mm
Drive hole Ø	9; 12 mm
Tool material	HSS E
Through-coolant	no
Type of product	Circular saw blade

## User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	37 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	22 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	20 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	15 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	11 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	11 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	11 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable	15 m/min	S
GG(G)	suitable	27 m/min	K
CuZn	suitable only under restricted conditions	400 m/min	N
Uni	suitable		
wet maximum	suitable		
dry	suitable only under restricted conditions		

Air

suitable only under  
restricted conditions