



HOLEX Pro Steel solid carbide drill, Weldon shank DIN 6535 HB, TiAlN, Ø DC h7 (mm or inch): 3,71-X



Order data

Order number	122502 3,71-X
GTIN	4062406661755
Item class	12F

Description

Version:

Straight major cutting edges and a **special flute profile** ensure good chip evacuation. The robust cutter geometry ensures high-performance drilling with good process reliability. A wide range of applications in steel materials thanks to a combination of tough ultra-fine grain carbide and extremely wear-resistant coating.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$. Delivery time: 10 weeks

Minimum order quantity: 5 pieces

Items made to order for a specific customer: Cancellation only up to a maximum of 3 working days after receipt of order acknowledgement. Items cannot be returned. We reserve the right to over-deliver or under-deliver by $\pm 10\%$ (minimum 1 piece).

Technical description

Number of cutting edges Z	2
Standard	DIN 6537 K
Shank Ø D_s	6 mm
Overall length L	66 mm
Flute length L_c	24 mm
Ø range	3.71 - 4.7 mm
Tolerance nominal Ø	h7
Series	Pro Steel

Coating	TiAlN
Tool material	Solid carbide
Version	4xD
Point angle	140 degrees
Shank	DIN 6535 HB to h6
Through-coolant	no
Machining strategy	HPC
Semi-Standard	yes
Colour ring	green
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Steel < 500 N/mm ²	suitable	115 m/min	P
Steel < 750 N/mm ²	suitable	105 m/min	P
Steel < 900 N/mm ²	suitable	85 m/min	P
Steel < 1100 N/mm ²	suitable	80 m/min	P
Steel < 1400 N/mm ²	suitable	60 m/min	P
INOX < 900 N/mm ²	suitable	30 m/min	M
INOX > 900 N/mm ²	suitable only under restricted conditions	25 m/min	M
GG	suitable	90 m/min	K
GGG	suitable	55 m/min	K
wet maximum	suitable		
dry	suitable		