

Garant
Solid carbide torus cutter HPC, TiAlN, Ø DC / R1: 8/0,5mm

Order data

Order number	206324 8/0,5
GTIN	4045197641380
Item class	11X

Description
Version:
GARANT Diabolo 70:

Special solid carbide substrate with extremely high tensile strength combined with **outstanding wear resistance** for optimum process reliability.

Newly developed **nano-crystalline high-tech coating for hard milling up to 70 HRC**. Very suitable **for continuous use** in tool and mould making.

Tolerances:

- **Corner radius: $R_1 = \pm 0.02$ mm.**

Application:

Due to the **special hard geometry** ideal for use on hardened materials from 60 HRC to 70 HRC.

For profile milling as a finishing operation.

(Plunge milling only to shallow depths).

Technical description

Cutting edge Ø D _c	8 mm
Feed f _z for side milling in steel < 70 HRC	0.06 mm
No. of teeth Z	6
Feed f _z for copy milling in steel < 70 HRC	0.06 mm
Corner radius R ₁	0.5 mm
Overhang length L ₁ incl. recess	24 mm
Recess Ø D ₁	7.85 mm
Shank Ø D _s	8 mm

Flute length L_c	8 mm
Overall length L	60 mm
Shank	DIN 6535 HA to h6
Helix angle	45 degrees
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	H
Tolerance nominal \varnothing	0 / -0.02
Direction of infeed	horizontal, oblique and vertical
Cutting width a_e for milling operation	0.05×D for copy milling
Cutting width a_e for milling operation	0.05×D for side milling
Through-coolant	no
Machining strategy	HPC
Shank tolerance	h6
Colour ring	red
Type of product	Torus cutter

User data

	Suitability	V_c	ISO code
Steel < 60 HRC	suitable only under restricted conditions	150 m/min	H
Steel < 65 HRC	suitable	110 m/min	H
Steel < 67 HRC	suitable	90 m/min	H
Steel < 70 HRC	suitable	80 m/min	H
dry	suitable		
Air	suitable		

Services

Shank grinding Type HB	129100 HB
------------------------	-----------

