



Solid carbide torus cutter HPC DIN 6535 HB, TiAlN, Ø DC / RS1: 12/0,3 mm

Order data

Order number	206358 12/0,3
GTIN	4045197527790
Item class	11X

Technical description

Machining strategy	HPC
Shank tolerance	h6
Tool material	Solid carbide
Milling profile	
Helix angle characteristic	unequal spacing
Tolerance nominal Ø	f8
Through-coolant	no
Cutting width a_e for milling operation	0.05×D for copy milling
Cutting width a_e for milling operation	0.2×D for side milling
Norm	DIN 6527
Direction of infeed	horizontal, oblique and vertical
Type	N
Colour ring	pink
Coating	TiAlN
Spacing of the cutters	unequal spacing
Series	
Type of product	

