


Solid carbide torus cutter HPC DIN 6535 HB, TiSi, Ø DC / R1: 12/0,5mm

Order data

Order number	206353 12/0,5
GTIN	4045197540317
Item class	12X

Description
Version:

Dimensions to factory standard and 35° spiral.

Special TiSi coating.

With balancing speed G 2.5.

Note:

NEW GENERATION AVAILABLE!

Recommended successor product is No. 206348

Technical description

Recess Ø D ₁	11.6 mm
Cutting edge Ø D _c	12 mm
Corner radius R ₁	0.5 mm
Feed f _z for copy milling in stainless steel > 900 N/mm ²	0.08 mm
Overhang length L ₁ incl. recess	36 mm
No. of teeth Z	4
Feed f _z for side milling in INOX > 900 N/mm ²	0.065 mm
Shank Ø D _s	12 mm
Flute length L _c	26 mm
Overall length L	83 mm
Shank	DIN 6535 HB to h6

Helix angle	35 degrees
Coating	TiSi
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Tolerance nominal \varnothing	f8
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Direction of infeed	horizontal, oblique and vertical
Cutting width a_e for milling operation	0.3×D for side milling
Cutting width a_e for milling operation	0.05×D for copy milling
Through-coolant	no
Machining strategy	HPC
Shank tolerance	h6
Colour ring	blue
Type of product	Torus cutter

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	250 m/min	P
Steel < 750 N/mm ²	suitable	230 m/min	P
Steel < 900 N/mm ²	suitable	200 m/min	P
Steel < 1100 N/mm ²	suitable	180 m/min	P
Steel < 1400 N/mm ²	suitable	170 m/min	P
TOOLOX 33	suitable	115 m/min	H
TOOLOX 44	suitable	80 m/min	H
INOX < 900 N/mm ²	suitable	90 m/min	M
INOX > 900 N/mm ²	suitable	80 m/min	M

Uni	suitable only under restricted conditions
wet maximum	suitable
wet minimum	Suitable
dry	Suitable only under restricted conditions
Air	suitable only under restricted conditions