

**Tipper truck RAL 7016 with discharge valve, Skip volume: 450l**

---

**Order data**

Order number	919923 450
GTIN	4017976247021
Item class	96D

---

**Description****Version:**

Oil-tight welded skip, on bearings for tipping.

Skip edge folded over twice at the top.

Chassis with integral fork lift slots, standing area and tilt lock.

2 fixed wheels and 2 castors (with parking brake) with TPE tyres, hubs with grooved ball bearings.

TOTALSTOP - central braking system to EN 1757-3 fitted as standard to the castors.

**Callout:**

Discharge valve

with sieve for separating liquids from solids.

Tipping action is operated manually.

For emptying using a forklift truck or when heavily loaded we recommend a self-tipper.

**Standard:**

**EN 1757-3**

**Colour:**

Anthracite RAL 7016 **powder-coated.**

---

**Technical description**

---

Material of wheel	TPE
Drain cock version	Delivery tap with sieve
Length	1374 mm
Fork insertion slots dimension C	603 mm
Fork insertion slots dimension D	72 mm
Filling edge height with rollers	733 mm
Weight	83 kg
Pull cord	no
Fork insertion slots dimension A	194 mm
Colour	RAL 7016 anthracite grey
welded oil-tight	yes
Number of wheels	4
Bucket length	1214 mm
Safe working load	750 kg
Skip volume	450 l
Standard	EN 1757-3
Bucket height	708 mm
Height	1072 mm
Fork-lift fork socket pitch B	203 mm
Internal dimension at intake: width	194 mm
Tipping mechanism	manual
Wheel Ø	200 mm
Tipping prevention	yes
Internal dimension at intake: height	72 mm
Bucket width	669 mm
Width	730 mm
with fork insertion slots	yes
Type of product	Tilting containers

