

Garant
Solid carbide milling cutter TPC, TiAlN, Ø f8 DC: 5mm

Order data

Order number	203102 5
GTIN	4045197814463
Item class	11X

Description

Version:

High-performance milling cutter with irregular cutter spacing and irregular helical pitch. Optimised bending strength due to the use of ultra-fine grain substrates. Offset chip breaker.

Note:

$a_e \max = 0.1 \times D$ for TPC machining. NEW GENERATION AVAILABLE! Recommended successor product is No. 203116. h_{\max} : The values stated in the table are maximum values. For finishing operations we recommend items No. 204012, 204014 and 204015.

Technical description

Overall length L	57 mm
Shank Ø D _s	6 mm
Cutting edge Ø D _c	5 mm
Shank	DIN 6535 HB to h6
Direction of infeed	horizontal and oblique
Flute length L _c	13 mm
Corner chamfer width at 45°	0.1 mm
Tolerance nominal Ø	f8
No. of teeth Z	7
Balance quality with shank	G 2.5 with HB
Helix angle	40 degrees

Average chip thickness h_{\max} for TPC milling in INOX < 900 N/mm ²	0.025 mm
Corner chamfer angle	45 degrees
Number of chip separators	0
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	0.1×D
Through-coolant	no
Machining strategy	TPC
Colour ring	blue
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	380 m/min	P
Steel < 750 N/mm ²	suitable	340 m/min	P
Steel < 900 N/mm ²	suitable	300 m/min	P
Steel < 1100 N/mm ²	suitable	230 m/min	P
INOX < 900 N/mm ²	suitable	240 m/min	M
INOX > 900 N/mm ²	suitable	170 m/min	M
wet maximum	Suitable		
wet minimum	Suitable only under restricted conditions		
Air	suitable		

