

**Garant****Flexible clamp, fixed, Type: 1****Order data**

Order number	360060 1
GTIN	4045197816139
Item class	310

**Description****Version:**

- **Steel base body with integral solid steel taper.**
- **Mechanical clamping mechanism.**
- **Tightening the lateral clamping bolt axially draws the component in with the respective clamping stud via 2 clamping wedges, and clamps it.**
- **Can be secured using steplessly adjustable clamps, T-nuts or zero point clamping system using clamping studs No. 360066.**
- **Pre-drilled for the zero point clamping system.**

The zero point clamping of the GARANT ZeroClamp system is an important function for modern production systems, especially in automated production. Thanks to a special contact interface, it ensures precise and reliable zero point repetition accuracy. The pneumatic clamping force of the system holds workpieces securely in the desired position, making it possible to change workpieces quickly and accurately without repositioning. This reduces the set-up effort and increases productivity. The zero point clamping of the GARANT ZeroClamp system is indispensable for efficient production processes. Find out more about the innovative technology from GARANT ZeroClamp and optimise your production.

**Application:**

Simple and exact positioning on the machine table. Clamping of complex components, e.g. for mould making.

**Optional extras:**

Clamping stud No. 360025 for size 120, torque wrench No. 656050 size 60, height element No. 360068.

## Technical description

Type	1
Length L	144 mm
Height H	100 mm
External Ø D	80 mm
Width B	99 mm
Torque	10 Nm
Series	ZeroClamp
Type of product	Spare part clamp

## Accessories

ZeroClamp clamping stud with internal thread Type 18M12	360025 18M12
ZeroClamp clamping stud with internal thread Type 16M10	360025 16M10
ZeroClamp clamping stud with internal thread Type 12M10	360025 12M10
ZeroClamp clamping stud with internal thread Type 18M16	360025 18M16
Torque wrench with reversible ratchet maximum torque 60 N·m	656050 60
ZeroClamp clamping stud with internal thread Type 25M10	360025 25M10
ZeroClamp clamping stud with internal thread Type 16M8	360025 16M8
Height element Type 1	360068 1