

**Garant**
**Solid carbide slot drill DIN 6535 HA, TiAlN, Ø e8 DC: 8mm**

**Order data**

Order number	202170 8
GTIN	4045197454690
Item class	11X

**Description**
**Version:**
**Eccentric relief ground.**

Dimensions similar to DIN 6527.

 Tolerance: Size nominal Ø  $D_c = e8$ .

**Technical description**

Feed $f_z$ for slot milling in steel < 900 N/mm <sup>2</sup>	0.04 mm
Recess Ø $D_1$	7.8 mm
Feed $f_z$ for side milling in steel < 900 N/mm <sup>2</sup>	0.045 mm
No. of teeth Z	3
Cutting edge Ø $D_c$	8 mm
Overhang length $L_1$ incl. recess	20 mm
Shank Ø $D_s$	8 mm
Overall length L	58 mm
Flute length $L_c$	12 mm
Direction of infeed	horizontal, oblique and vertical
Correction factor for $v_c$	1.25
Shank	DIN 6535 HA to h6
Tolerance nominal Ø	e8

Helix angle	45 degrees
Corner chamfer angle	90 degrees
Coating	TiAlN
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Cutting width $a_e$ for milling operation	0.5×D for side milling
Cutting width $a_e$ for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Colour ring	without
Type of product	End / face mill

## User data

	Suitability	$V_c$	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	280 m/min	N
Alu > 10% Si	suitable only under restricted conditions	200 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	120 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	105 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	100 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	70 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	60 m/min	P
Steel < 55 HRC	suitable only under restricted conditions	35 m/min	H
INOX < 900 N/mm <sup>2</sup>	suitable	80 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	60 m/min	M
GG(G)	suitable	90 m/min	K
Uni	suitable		

wet maximum	suitable
wet minimum	suitable only under restricted conditions
dry	suitable only under restricted conditions
<b>Services</b>	
Shank grinding Type HB	129100 HB