



Tap wrench, adjustable reinforced, Type: 1.1/2



Order data

Order number	148150 1.1/2
GTIN	4045197814876
Item class	12L

Description

Version:

With hardened jaws and steel grips. For use in confined spaces one steel handle can be unscrewed.

Strengthened version. All dimensions **with high-quality forged steel body and all-steel handles.**

Standard: DIN 1814

Capacity □: 2 - 8 mm

for hand taps DIN 352: M1 – M12

for hand reamer Ø DIN 206: 2.5 - 9.5 mm

Overall length: 200 mm

Technical description

Overall length	200 mm
Capacity □	2 - 8 mm
for hand taps DIN 352	M1 – M12
for hand reamer Ø DIN 206	2.5 - 9.5 mm
Standard	DIN 1814
Type of product	Tap wrench