


Garant
GARANT Diabolo solid carbide torus cutter HPC, TiAlN, Ø e8 DC / R1: 8/0,5mm

Order data

Order number	206422 8/0,5
GTIN	4045197599278
Item class	11X

Description
Version:
GARANT Diabolo:

Special geometry, coating and carbide for hard machining.

Tolerance: Corner radius $R_1 = \pm 0.005 \text{ mm}$.

Tolerance: Corner radius $RS_1 = \pm 0.005 \text{ mm}$.

Application:

For peripheral milling as a **finishing operation** (plunge milling only to shallow depths).

Technical description

Corner radius R_1	0.5 mm
No. of teeth Z	6
Feed f_z for side milling in steel < 65 HRC	0.018 mm
Cutting edge $\varnothing D_c$	8 mm
Shank $\varnothing D_s$	8 mm
Flute length L_c	19 mm
Overall length L	63 mm
Shank	DIN 6535 HA to h6
Helix angle	45 degrees
Series	Diabolo
Coating	TiAlN

Tool material	Solid carbide
Standard	DIN 6527
Type	H
Tolerance nominal \varnothing	e8
Helix angle characteristic	unequal spacing
Direction of infeed	horizontal and oblique
Cutting width a_e for milling operation	0.05×D for side milling
Cutting width a_e for milling operation	0.05×D for copy milling
Through-coolant	no
Machining strategy	HPC
Shank tolerance	h6
Colour ring	red
Type of product	Torus cutter

User data

	Suitability	V_c	ISO code
Steel < 1400 N/mm ²	suitable	170 m/min	P
Steel < 50 HRC	suitable	170 m/min	H
Steel < 55 HRC	suitable	170 m/min	H
Steel < 60 HRC	suitable	145 m/min	H
Steel < 65 HRC	suitable	100 m/min	H
wet maximum	suitable only under restricted conditions		
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	suitable		

Services

Shank grinding Type HB	129100 HB
------------------------	-----------

