




Top jaws set, 3 pieces, for chuck type: 254



Order data

Order number	313745 254
GTIN	4062406699307
Item class	32R

Description

Version:

Soft top jaws, long, serration 1.5×60°.

Precision milled slots and serration, **not burnished**.

Bevelled for small clamping Ø.

Material:

Quality product made of 16MnCr5.

Suitable for:

Heavy-duty chucks from Schunk, Röhm and other heavy-duty chuck manufacturers.

Optional extras:

T-nuts No. 313505 – 313605.

Note:

- **When fitting to a chuck, please check serrations, slot width (D), and hole spacing (a, b).**
- **Aluminium top jaws on request.**

Technical description

Width B	40 mm
Hole centre spacing a	30 mm
for thread DIN 912	M12
for chuck type	254 mm
Height H	40 mm
Slot width D	16 mm

Bore spacing b	30 mm
Length L	125 mm
suitable for colour code	Schunk heavy-duty chucks and jaws
Type of product	Heavy-duty lathe chuck jaws