

Garant

Solid carbide torus cutter HPC, TiAlN, Ø f8 DC / RS1: 8/0,5 mm



Order data

Order number	206510 8/0,5
GTIN	4045197655615
Item class	11X

Description

Version:

Special coating for the best tool life and high metal removal rates.

For milling **Ni-based alloys**.

No. of teeth Z: 6

Helix angle: 50 degrees

Shank: DIN 6535 HA to h6

Balance quality with shank: G 2.5 with HA

No. of teeth Z: 6

Flute length L_c : 19 mm

Corner radius R_1 : 0.5 mm

Overall length L: 63 mm

Shank Ø D_s : 8 mm

Feed f_z for copy milling in Inconel®: 0.029 mm

Technical description

Cutting edge Ø D_c	8 mm
Feed f_z for copy milling in Inconel®	0.029 mm
Corner radius R_1	0.5 mm
No. of teeth Z	6
Shank Ø D_s	8 mm
Flute length L_c	19 mm
Overall length L	63 mm

Balance quality with shank	G 2.5 with HA
Shank	DIN 6535 HA to h6
Helix angle	50 degrees
Coating	TiAlN
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Tolerance nominal \varnothing	f8
Spacing of the cutters	unequal spacing
Direction of infeed	horizontal, oblique and vertical
Cutting width a_e for milling operation	0.05×D for copy milling
Cutting width a_e for milling operation	0.2×D for side milling
Through-coolant	no
Machining strategy	HPC
Shank tolerance	h6
Colour ring	pink
Type of product	End mill

Services

Shank recess Type FRST	209900 FRST
Shank grinding Type HB	129100 HB