

Garant
Side milling cutter HSS-Co5, uncoated, \varnothing ×width ± 0.1 ×k11: 63X5 mm

Order data

Order number	185005 63X5
GTIN	4045197546524
Item class	11U

Description
Version:
Side milling cutter similar to DIN 885-A.

Pairs of milling cutters: Cutters with the same \varnothing and same number of teeth can be combined as a set and adjusted to the required width. Since the cutters have no raised bore collar, the staggered teeth mesh with each other.

2-piece sets are particularly economical. By reversing the side milling cutters, both side edges of each cutter can be used.

Note:

- **Do not clamp the cutters in a set without a sufficiently thick arbor spacer ring, otherwise the cutters will be damaged.**
- **See Group 30 for suitable arbor spacer rings.**

Cutters are manufactured with external \varnothing to a tolerance ± 0.1 mm When using 2 cutters as a set and higher precision is required, the cutters must be ground as a set.

Slots milled from solid: f_z for $a_e = 0.1 \times D$.

Through-coolant: no

Bore \varnothing H6 d₁: 22 mm

No. of teeth Z: 14

Collar thickness $b \pm 0.1$: 3.5 mm

Collar \varnothing d₂ ± 1 : 40 mm

Tooth height Zh: 11.5 mm

Capability of combining 2 cutters of the same width A/B: 5 mm

Technical description

Collar $\varnothing d_2 \pm 1$	40 mm
Capability of combining 2 cutters of different width A	5 mm
Bore $\varnothing H6 d_1$	22 mm
No. of teeth Z	14
Capability of combining 2 cutters of different width B	6 mm
Capability of combining 2 cutters of different width, results in overall width E	9.6 - 10.8 mm
Cutting edge $\varnothing D_c$	63 mm
Feed f_z in steel $< 900 \text{ N/mm}^2$	0.05 mm
Capability of combining 2 cutters of the same width A/B	5 mm
Tooth height Zh	11.5 mm
Capability of combining 2 cutters of the same width, results in overall width E	9.1 - 9.8 mm
Collar thickness $b \pm 0.1$	3.5 mm
Cutting width	5 mm
Shank type	with bore
Coating	uncoated
Tool material	HSS Co 5
Standard	DIN 885 A
Type	N
Tolerance nominal \varnothing	± 0.1
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Through-coolant	no
Colour ring	without
Type of product	Side milling cutter

