Garant

GARANT Master Tap machine tap HSS-E-PM Form B 7GX, AlTiX, M: M2



Order data

Order number	132728 M2
GTIN	4062406710934
Item class	111

Description

Version:

Universal taps, designed for use in a wide spectrum of materials with high process reliability.

- HSS-E-PM tool material for a high degree of wear resistance.
- · Reduced coefficient of friction due to the new high-performance coating.
- · Special geometry for optimum swarf evacuation.

Tolerance class: 7GX

Application:

For components which are galvanised or shrink slightly when hardened.

Recommendation:

We recommend increasing the size of the tapping hole \varnothing by the tolerance allowance. Thread type: M Tool material: HSS E PM Standard: DIN 371 Tolerance class: 7GX Thread pitch: 0.4 mm Overall length L: 45 mm Shank \varnothing D_s: 2.8 mm Shank square \Box : 2.1 mm Tapping hole \varnothing : 1.6 mm

Technical description

Shank Ø D _s	2.8 mm
Thread type	М
Standard	DIN 371
Tool material	HSS E PM

© Hoffmann GmbH Qualitätswerkzeuge

Thread pitch	0.4 mm		
Thread size	M2		
Tapping hole Ø	1.6 mm		
Tolerance class	7GX		
Number of clamping slots	2		
Number of cutting edges Z	2		
Shank square 🗆	2.1 mm		
Thread depth	6 mm		
Thread Ø	2 mm		
Overall length L	45 mm		
Coating	AlTiX		
Flank angle	60 °		
Thread standard	DIN 13		
Taper lead form	В		
Shank	Plain shank with h9		
Through-coolant	no		
Application for type of drilling	up to 3×D for through holes		
Cutting direction	right-hand		
Type of threading tool	Machine tap for dynamic machining		
Colour ring	green		
Series	Master Tap		
Type of product	Тар		

User data

	Suitability	V _c	ISO code
Alu plastics	suitable	30 m/min	Ν
Aluminium (short chipping)	suitable	35 m/min	Ν
Alu > 10% Si	suitable	20 m/min	Ν

© Hoffmann GmbH Qualitätswerkzeuge

Steel < 500 N/mm ²	suitable	30 m/min	Р
Steel < 750 N/mm²	suitable	30 m/min	Р
Steel < 900 N/mm ²	suitable	25 m/min	Р
Steel < 1100 N/mm²	suitable	12 m/min	Р
Steel < 1400 N/mm ²	suitable	8 m/min	Р
INOX < 900 N/mm ²	suitable	10 m/min	М
INOX > 900 N/mm ²	suitable	8 m/min	М
GG(G)	suitable	20 m/min	К
CuZn	suitable	20 m/min	Ν
Uni	suitable		
Oil	suitable		
wet maximum	suitable		