# Garant

#### GARANT Master Tap machine tap HSS-E-PM Form C 6H+0.1, AITiX, M: M3

Garant Garant

## Order data

Order number	136164 M3
GTIN	4062406710972
Item class	111

## Description

#### Version:

Universal taps, designed for use in a wide spectrum of materials with high process reliability.

- HSS-E-PM tool material for a high degree of wear resistance.
- · Reduced coefficient of friction due to the new high-performance coating.
- · Special geometry for optimum swarf evacuation.
- Tolerance class: ISO 2/6H+0.1

#### Application:

For components which are galvanised or shrink slightly when hardened.

#### **Recommendation:**

We recommend increasing the size of the tapping hole  $\varnothing$  by the tolerance allowance. Thread type: M Tool material: HSS E PM Standard: DIN 371 Tolerance class: ISO 2 6H + 0.1 Thread pitch: 0.5 mm Overall length L: 56 mm Shank  $\varnothing$  D<sub>s</sub>: 3.5 mm Shank square  $\Box$ : 2.7 mm Tapping hole  $\varnothing$ : 2.5 mm

### **Technical description**

Thread Ø	3 mm
Number of cutting edges Z	3
Shank square 🗆	2.7 mm
Thread depth	7.5 mm

© Hoffmann GmbH Qualitätswerkzeuge

Number of clamping slots	3	
Thread pitch	0.5 mm	
Tolerance class	ISO 2 6H + 0.1	
Tapping hole Ø	2.5 mm	
Standard	DIN 371	
Overall length L	56 mm	
Thread size	M3	
Tool material	HSS E PM	
Shank Ø D <sub>s</sub>	3.5 mm	
Thread type	М	
Coating	AlTiX	
Flank angle	60 °	
Thread standard	DIN 13	
Taper lead form	C	
Helix angle	40 °	
Shank	Plain shank with h9	
Through-coolant	no	
Application for type of drilling	up to 2.5×D for blind holes	
Cutting direction	right-hand	
Type of threading tool	Machine tap for dynamic machining	
Colour ring	green	
Series	Master Tap	
Type of product	Тар	

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu plastics	suitable	30 m/min	Ν
Aluminium (short chipping)	suitable	35 m/min	Ν

© Hoffmann GmbH Qualitätswerkzeuge

Alu > 10% Si	suitable	20 m/min	Ν
Steel < 500 N/mm <sup>2</sup>	suitable	30 m/min	Р
Steel < 750 N/mm <sup>2</sup>	suitable	30 m/min	Р
Steel < 900 N/mm <sup>2</sup>	suitable	25 m/min	Р
Steel < 1100 N/mm²	suitable	12 m/min	Р
Steel < 1400 N/mm <sup>2</sup>	suitable	8 m/min	Р
INOX < 900 N/mm <sup>2</sup>	suitable	10 m/min	М
INOX > 900 N/mm <sup>2</sup>	suitable	8 m/min	М
GG(G)	suitable	20 m/min	К
CuZn	suitable	20 m/min	Ν
Uni	suitable		
Oil	suitable		
wet maximum	suitable		