



Safety coupling External thread, Connection external thread: 1/4in



Order data

| | |
|--------------|---------------|
| Order number | 080276 1/4 |
| GTIN | 7391390419064 |
| Item class | 08A |

Description

Version:

Steel couplings have many advantages in pneumatic systems compared to standard brass couplings:

- **Easy to use with only one hand with low coupling force.**
- **High flow rates as a consequence of very low pressure drop.**
- **Long working life due to surface treatment and hardened components with tight manufacturing tolerances.**
- **Cost-effectiveness – the amortisation time is 2 years at the most.**

The **eSafe safety coupling** satisfies the ISO standard 4414 and EN 983. It is first depressurised and then decoupled in a second step (no whiplash). New improved single-handed operation. Rate of flow: 950 ltr/min, maximum operating pressure 16 bar. Complies with ISO standard B.

Application:

For improving the performance, economics, and safety of industrial compressed air installations.

Note:

The CEJN series 310 is suitable for the markets of Benelux, France, North America and Norway.

Technical description

| | |
|----------------------------|----------------|
| Material | Steel coupling |
| Connection external thread | 1/4 in |
| Flow rate | 950 l/min |
| maximum operating pressure | 16 bar |

Type of product

Coupling