




## Top jaws set, 3 pieces, for chuck type: 400



### Order data

Order number	313405 400
GTIN	4019208193434
Item class	32R

### Description

#### Version:

Clamping jaws with sharp serrations 1/16 inch × 90°.

**Precision milled** slots and serrations, **not burnished**.

#### Material:

Quality product made of 16MnCr5.

#### Suitable for:

**Heavy-duty chucks** from Schunk, Röhmm and other heavy-duty chuck manufacturers.

#### Optional extras:

T-nuts No. 313505 – 313605.

#### Note:

- **When fitting to a chuck, please check serrations, slot width (D), and hole spacing (a, b).**
- **Aluminium top jaws on request.**

### Technical description

Hole centre spacing a	20 mm
Length L	130 mm
Slot width D	25.5 mm
Height H	80 mm
Bore spacing b	31 mm
for thread DIN 912	M20

Width B	50 mm
also suitable for chuck type	500/630 mm
Type of product	Heavy-duty lathe chuck jaws