




## Top jaws set, 3 pieces, for chuck type: 170



### Order data

Order number	313745 170
GTIN	4067263151333
Item class	32R

### Description

#### Version:

Soft top jaws, long, serration 1.5×60°.

**Precision milled** slots and serration, **not burnished**.

Bevelled for small clamping Ø.

#### Material:

Quality product made of 16MnCr5.

#### Suitable for:

**Heavy-duty chucks** from Schunk, Röhm and other heavy-duty chuck manufacturers.

#### Optional extras:

T-nuts No. 313505 – 313605.

#### Note:

- **When fitting to a chuck, please check serrations, slot width (D), and hole spacing (a, b).**
- **Aluminium top jaws on request.**

### Technical description

Width B	31 mm
for thread DIN 912	M10
Height H	32 mm
Hole centre spacing a	15 mm
Bore spacing b	20 mm
for chuck type	170 mm

Length L	82 mm
Slot width D	12 mm
suitable for colour code	Schunk heavy-duty chucks and jaws
Type of product	Heavy-duty lathe chuck jaws