


Mitutoyo**Precision bore gauge with dial indicator, Measuring range: 18-35mm****Order data**

Order number	435203 18-35
GTIN	4946368854885
Item class	44A

Description**Version:**

Self-centring precision bore gauge with three-point contact. Gauge holder and dial indicator matt chrome-plated. Shock-resistant plastic dial indicator housing. Gauge holder compensated for hand temperature. The gauge is set to the bore \varnothing by exchangeable contact points of different lengths and intermediate rings.

Measuring pins with spherical carbide tips.

Application:

Dial bore gauge for checking bores for \varnothing accuracy, cylindrical form, and roundness.

Supplied with:

Supplied with dial indicator No. 432051 size 10/58 with 1/100-mm scale.

Technical description

Measuring range	18 - 35 mm
Repetition accuracy without dial gauge	0.5 μ m
Centring plate width	12.7 mm
Measurement depth	100 mm
Number of contact points	9

Standard	Manufacturer's standard
Packaging	sturdy box
Calibration	C1
Calibration	C4
Type of product	2-point precision bore gauge

Services

Calibration Precision bore gauge (types B + C) maximum measuring range 60 mm	023210 60
Calibration Dial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 10 mm	023000 10
DAkkS calibration Precision bore gauge (types B + C) maximum measuring range 60 mm	023220 60
DAkkS calibration Dial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 12,5 mm	023010 12,5

Accessories

Spacer ring inner Ø 5.3 mm Ring width 0,5 mm	435220 0,5
Spacer ring inner Ø 5.3 mm Ring width 1 mm	435220 1