

Garant
Radius cutter, Weldon shank, Type: 2

Order data

Order number	216825 2
GTIN	4062406706425
Item class	210

Description
Application:

For producing convex radii on components. The slim and compact design permits a wide variety of applications and is particularly suitable for use in deep cavities.

Tool exchange: PowerCard

Through-coolant: no

Radius milling: forwards

Number of cutting edges Z: 2

Shank $\varnothing D_s$: 20 mm

maximum \varnothing : 22 mm

Overhang L_1 : 35 mm

Overall length L_{tot} : 120 mm

minimum radius: 3 mm

Technical description

Insert screw	219879 1 (TX15; 3Nm)
suitable indexable insert	216841 3 - 5
Through-coolant	no
Overall length L_{tot}	120 mm
Number of cutting edges Z	2
Overhang L_1	35 mm
minimum radius	3 mm

maximum Ø	22 mm
Shank Ø D _s	20 mm
Maximum radius	5 mm
Radius milling	forwards
Shank type	Weldon shank
Tool exchange	PowerCard

Accessories

PrecisionBit for Torx®, shank E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver, fixed setting set torque 3,0 N·m	211750 3,0