

## Garant

**GARANT Master Alu FEED solid carbide drill, Weldon shank DIN 6535 HB, uncoated, Ø DC h7: 7,45mm**



### Order data

Order number	122591 7,45
GTIN	4062406724610
Item class	11E

### Description

#### Version:

**3-cutter tool**, specially developed for use at **very high feed rates** in aluminium. Outstandingly suitable for machines with **high power consumption** and stable machining conditions.

- **Specially developed cutter geometry, designed for very high feed rates, reduced cutting pressure and controlled chip breaking.**
- **Precision flute profile for reliable evacuation of chips.**
- **Achieve outstanding feed rates and tool life thanks to the third cutting edge.**

The sector-leading technology of the drill point for the tool guarantees optimum self-centring behaviour and permits spot drilling on irregular surfaces. 3 guidance lands guarantee a stable exit from the hole and an exact roundness of the hole.

#### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

### Technical description

Shank Ø D <sub>s</sub>	8 mm
Tolerance nominal Ø	h7
Overall length L	91 mm
Nominal Ø D <sub>c</sub>	7.45 mm
Standard	DIN 6537
Flute length L <sub>c</sub>	53 mm
recommended maximum drilling depth L <sub>2</sub>	41.8 mm

Number of cutting edges Z	3
Feed f in aluminium short-chipping	0.84 mm/rev.
Series	Master Alu
Coating	uncoated
Tool material	solid carbide
Version	6xD
Type	W
Point angle	130 degrees
Shank	DIN 6535 HB to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	yellow
Type of product	Jobber drill

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu plastics	suitable	300 m/min	N
Aluminium (short chipping)	suitable	250 m/min	N
Alu > 10% Si	suitable	200 m/min	N
CuZn	suitable	200 m/min	N
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		