

Garant

GARANT Master Form Steel fluteless machine tap with oil grooves HSS-E-PM, TiAlN, UNC: 3/8-16



Order data

Order number	139485 3/8-16
GTIN	4062406707088
Item class	111

Description

Version:

The latest generation of **high-performance fluteless taps**, specially developed for **use in steel materials**.

- **Optimised polygon geometry for a lower torque.**
- **Multi-layer HIPIMS coating for high wear resistance.**
- **HSS-E-PM substrate for exceptional process reliability.**

DIN 2174 (\approx DIN 371 \leq 3/8; \approx DIN 376 \geq 7/16).

Form E (lead-in 1.5 – 2 turns). For deep threads with short lead-in. The thread is tapped almost to the bottom of the hole.

Application:

For UNC unified coarse threads ASME–B1.1.

Thread pitch: 1.587 mm

Threads per inch: 16

Thread \varnothing : 9.53 mm

Overall length L: 100 mm

Shank \varnothing D_s: 10 mm

Shank square \square : 8 mm

Technical description

Thread \varnothing	9.53 mm
Shank \varnothing D _s	10 mm
Tapping hole \varnothing guide value	8.8 mm
Thread depth	28.59 mm

Shank square <input type="checkbox"/>	8 mm
Number of cutting edges Z	6
Number of clamping slots	6
Thread pitch	1.587 mm
Overall length L	100 mm
Threads per inch	16
Coating	TiAlN
Thread type	UNC
Flank angle	60 °
Tool material	HSS E PM
Standard	DIN 2174
Tolerance class	2BX
Taper lead form	E
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of product	Fluteless tap

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable	38 m/min	N
Steel < 500 N/mm ²	suitable	37 m/min	P
Steel < 750 N/mm ²	suitable	35 m/min	P
Steel < 900 N/mm ²	suitable	27 m/min	P
Steel < 1100 N/mm ²	suitable	18 m/min	P
Steel < 1400 N/mm ²	suitable	12 m/min	P

INOX < 900 N/mm ²	suitable	12 m/min	M
INOX > 900 N/mm ²	suitable	7 m/min	M
CuZn	suitable	22 m/min	N
Oil	suitable		
wet maximum	suitable		
wet minimum	suitable		