

Garant

GARANT Master Form Steel fluteless machine tap with oil grooves HSS-E-PM, TiAlN, UNF: 5/16-24



Order data

Order number	139495 5/16-24
GTIN	4062406707194
Item class	111

Description

Version:

The latest generation of **high-performance fluteless taps**, specially developed for **use in steel materials**.

- **Optimised polygon geometry for a lower torque.**
- **Multi-layer HIPIMS coating for high wear resistance.**
- **HSS-E-PM substrate for exceptional process reliability.**

DIN 2174 (\approx DIN 371 \leq 3/8; \approx DIN 376 \geq 7/16).

Form E (lead-in 1.5 – 2 turns). For deep threads with short lead-in. The thread is tapped almost to the bottom of the hole.

Application:

For UNF unified fine threads ASME–B1.1.

Thread pitch: 1.058 mm

Threads per inch: 24

Thread \varnothing : 7.94 mm

Overall length L: 90 mm

Shank \varnothing D_s: 8 mm

Shank square \square : 6.2 mm

Technical description

Shank \varnothing D _s	8 mm
Thread \varnothing	7.94 mm
Shank square \square	6.2 mm
Thread pitch	1.058 mm

Tapping hole Ø guide value	7.45 mm
Thread depth	23.28 mm
Overall length L	90 mm
Number of clamping slots	5
Number of cutting edges Z	5
Threads per inch	24
Coating	TiAlN
Thread type	UNF
Flank angle	60 °
Tool material	HSS E PM
Standard	DIN 2174
Tolerance class	2BX
Taper lead form	E
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of product	Fluteless tap

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable	38 m/min	N
Steel < 500 N/mm ²	suitable	37 m/min	P
Steel < 750 N/mm ²	suitable	35 m/min	P
Steel < 900 N/mm ²	suitable	27 m/min	P
Steel < 1100 N/mm ²	suitable	18 m/min	P
Steel < 1400 N/mm ²	suitable	12 m/min	P

INOX < 900 N/mm ²	suitable	12 m/min	M
INOX > 900 N/mm ²	suitable	7 m/min	M
CuZn	suitable	22 m/min	N
Oil	suitable		
wet maximum	suitable		
wet minimum	suitable		