

**Garant**
**Boring bar carbide, right-hand, Shank  $\varnothing$  / insert size: 8/05mm**


## Order data

Order number	261376 8/05
GTIN	4062406710835
Item class	21T

## Technical description

Minimum pre-drill $\varnothing D_{\min}$	8 mm
Setting angle $\kappa$	140 degrees
suitable indexable insert	VC.. 0501..
Insert size	5 mm
Centre offset $L_3$	3 mm
Clamping height $L_2$	7.5 mm
Head length $L_1$	26 mm
Pack of insert screws	269028 26
ISO code toolholder	E08F SVOCR/L05
Overall length L	80 mm
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar