

Garant

GARANT Master Alu FEED solid carbide drill, plain shank DIN 6535 HA, uncoated, Ø DC h7: 5,3mm


Order data

Order number	122590 5,3
GTIN	4062406711542
Item class	11E

Description
Version:

3-cutter tool, specially developed for use at **very high feed rates** in aluminium. Outstandingly suitable for machines with **high power consumption** and stable machining conditions.

- **Specially developed cutter geometry, designed for very high feed rates, reduced cutting pressure and controlled chip breaking.**
- **Precision flute profile for reliable evacuation of chips.**
- **Achieve outstanding feed rates and tool life thanks to the third cutting edge.**

The sector-leading technology of the drill point for the tool guarantees optimum self-centring behaviour and permits spot drilling on irregular surfaces. 3 guide chamfers guarantee a stable exit from the hole and an exact roundness of the hole.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

HB and HE shanks are available at the same price as HA.

For **HB**: use order **No. 122591**.

For **HE**: use order **No. 122590 + 129100HE**.

Technical description

recommended maximum drilling depth L_2	36.1 mm
Nominal Ø D_c	5.3 mm
Tolerance nominal Ø	h7
Standard	DIN 6537
Overall length L	82 mm

Shank $\varnothing D_s$	6 mm
Flute length L_c	44 mm
Number of cutting edges Z	3
Feed f in aluminium short-chipping	0.66 mm/rev.
Series	Master Alu
Coating	uncoated
Tool material	solid carbide
Version	6xD
Type	W
Point angle	130 degrees
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	yellow
Type of product	Jobber drill

User data

	Suitability	V_c	ISO code
Alu plastics	suitable	300 m/min	N
Aluminium (short chipping)	suitable	250 m/min	N
Alu > 10% Si	suitable	200 m/min	N
CuZn	suitable	200 m/min	N
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		

Services

Shank grinding Type HE	129100 HE
------------------------	-----------

