


Garant**GARANT Master eco clamping toolholder short, left-hand, Shank / insert size: 25/16mm****Order data**

Order number	251405 25/16
GTIN	4062406736194
Item class	21U

Description**Version:**

Highly efficient cooling directly on the cutter and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master eco toolholders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Series	Master Eco
Pin	259049 8
ISO code toolholder	MTJNR/L 2525X16
Shank size	25 mm
Functional width L ₄	32 mm
Screw for clamping claw	259021 6
Shim	259033 9
Clamping claw	259038 20
Overall length L	105 mm

suitable indexable insert	TN.. 1604..
Insert size	16 mm
Head length L ₁	35 mm
Standard	Works standard
Application type	left-hand
Through-coolant	yes
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500