

Garant

Mechanical jointed measuring stand (without magnetic base), Throat: 290mm



Order data

Order number	441610 290
GTIN	4062406729752
Item class	41D

Description

Version:

Mechanic measuring stand with central clamping – all joints are rigidly clamped by means of the central boring head. Clamping force can be steplessly adjusted. **Large rubberised handwheel** (Ø approx. 45 mm or approx. 55 mm) for easy tightening and releasing of the clamp. The dial indicator mounting on the jointed arm rotates 360°, can be twisted 180° and is suitable for dial indicators with shank Ø 6 and 8 mm or vee block. Connection thread for magnetic base M8, connection thread for jointed arm at the top M6.

Optional extras:

Holder for measuring stand No. 442100 and 442104.

Technical description

Connection thread	M8
Length of jointed arm L ₂	110 mm
Throat	290 mm
Length of jointed arm L ₁	130 mm

Type of product

measuring stand

Accessories

Mechanical measuring stand (with magnetic base) Throat
290 mm

441600 290