

**Garant**
**Mechanical measuring stand (with magnetic base), Throat: 240mm**

**Order data**

Order number	441600 240
GTIN	4062406735135
Item class	41D

**Description**
**Version:**

**Mechanic measuring stand with central clamping** – all joints are rigidly clamped by means of the central boring head. Clamping force can be steplessly adjusted. **Large rubberised handwheel** (Ø approx. 45 mm or approx. 55 mm) for easy tightening and releasing of the clamp. The dial indicator mounting on the jointed arm rotates 360°, can be twisted 180° and is suitable for dial indicators with shank Ø 6 and 8 mm or vee block. Connection thread for magnetic base M8, connection thread for jointed arm at the top M6.

Stand with magnetic base and **ergonomic rotary switch**. High performance ferrite magnet with ground contact faces on the back and ground Vee underneath for placing on shafts and cylindrical bodies. **Plastic enclosure** of the magnetic base for easy handling, enhanced shock protection and thermal insulation.

**Supplied with:**

Measuring stand with magnetic base No. 440620 size 1.

**Optional extras:**

Holder for measuring stand No. 442100 and 442104.

**Technical description**

Connection thread	M8
Alignment of connecting thread	side
Magnetic force	1000 N
Length of jointed arm L <sub>2</sub>	101 mm
Throat	240 mm
Length of jointed arm L <sub>1</sub>	110 mm
Type of product	measuring stand

---

## Accessories

Magnetic base Type 1	440620 1
----------------------	----------