

Garant
Solid carbide ball nose slot drill, uncoated, Ø f8 DC: 16mm

Order data

Order number	207028 16
GTIN	4045197596703
Item class	11X

Description
Version:

Additionally **polish ground** in the flutes for **outstanding chip evacuation** in long-chipping aluminium components.

Dimensions similar to **DIN 6527**.

Technical description

No. of teeth Z	2
Recess Ø D ₁	15 mm
Cutting edge Ø D _c	16 mm
Feed f _z for copy milling in short-chipping aluminium	0.15 mm
Overhang length L ₁ incl. recess	92 mm
Shank Ø D _s	16 mm
Overall length L	150 mm
Flute length L _c	30 mm
Helix angle	45 degrees
Radius R	8 mm
Coating	uncoated
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	W

Tolerance nominal \varnothing	f8
Direction of infeed	horizontal, oblique and vertical
Cutting width a_e for milling operation	0.03×D for copy milling
Shank	DIN 6535 HA to h6
Balance quality with shank	G 2.5 with HA
Through-coolant	no
Colour ring	yellow
Type of product	Ball-nosed slot drill

User data

	Suitability	V_c	ISO code
Aluminium	Suitable	220 m/min	N
Aluminium (short chipping)	suitable	170 m/min	N
Alu > 10% Si	suitable	130 m/min	N
PMMA acrylic	Suitable	180 m/min	N
PE-HD	Suitable	140 m/min	N
PA 66	Suitable	180 m/min	N
PEEK	Suitable	130 m/min	N
PF 31	Suitable	120 m/min	N
Honeycomb sandwich	suitable only under restricted conditions	180 m/min	N
Cu	Suitable	140 m/min	N
CuZn	Suitable	180 m/min	N
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable only under restricted conditions		

Air

suitable only under
restricted conditions

Services

Shank grinding Type HB

129100 HB