

Garant**GARANT Master Alu Feed solid carbide drill, plain shank DIN 6535 HB, DLC, Ø DC h7: 11,8mm****Order data**

Order number	122596 11,8
GTIN	4062406725280
Item class	11E

Description**Version:**

3-cutter tool, specially developed for use at **very high feed rates** in aluminium. Outstandingly suitable for machines with **high power consumption** and stable machining conditions.

- **Specially developed cutter geometry, designed for very high feed rates, reduced cutting pressure and controlled chip breaking.**
- **Precision flute profile for reliable evacuation of chips.**
- **Achieve outstanding feed rates and tool life thanks to the third cutting edge.**

The sector-leading technology of the drill point for the tool guarantees optimum self-centring behaviour and permits spot drilling on irregular surfaces. 3 guidance lands guarantee a stable exit from the hole and an exact roundness of the hole.

With DLC coating – for longer tool lives, especially with aluminium with a higher Si content.

Coating on order – no return. Delivery time approx. 3 weeks if the basic item is available ex stock. Please note the minimum order quantity.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Technical description

Nominal Ø D_c	11.8 mm
Overall length L	118 mm
Feed f in aluminium short-chipping	1.16 mm/rev.
Number of cutting edges Z	3
Standard	DIN 6537 L

Data sheet

Tolerance nominal Ø	h7
Shank Ø D _s	12 mm
Flute length L _c	71 mm
recommended maximum drilling depth L ₂	53.3 mm
Series	Master Alu
Coating	DLC
Tool material	solid carbide
Version	6×D
Type	W
Point angle	130 degrees
Shank	DIN 6535 HB to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	yellow
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Alu plastics	suitable	300 m/min	N
Aluminium (short chipping)	suitable	250 m/min	N
Alu > 10% Si	suitable	200 m/min	N
CuZn	suitable	200 m/min	N
wet maximum	suitable		
wet minimum	suitable		