



## HOLEX CleverDrill HSS jobber drill N, uncoated, Ø DC h8 (mm or inch): 0,7



### Order data

Order number	114031 0,7
GTIN	4062406743437
Item class	12B

### Description

#### Version:

**HOLEX CleverDrill:** Sturdy drills for all standard applications. Improved spot drilling behaviour due to cross-ground form. Standard core thickness and core taper. Profile ground. Surface: Bronze-coloured tempered helical flutes.

#### Recommendation:

##### Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c$$

#### Note:

##### Successor product to No. 114030.

Size 13.2 – 20: With stepped shank Ø 12.7 mm.

Through-coolant: no

Standard: DIN 338

Tolerance nominal Ø: h8

Point angle: 118 °

Shank: Plain shank

Number of cutting edges Z: 2

recommended maximum drilling depth  $L_2$ : 8 mm

Flute length  $L_c$ : 9 mm

Overall length L: 28 mm

Shank Ø  $D_s$ : 0.7 mm

Feed f in steel < 750 N/mm<sup>2</sup>: 0.03 mm/rev.

### Technical description

Tolerance nominal Ø	h8
recommended maximum drilling depth $L_2$	8 mm

Flute length $L_c$	9 mm
Shank $\varnothing D_s$	0.7 mm
Standard	DIN 338
Feed $f$ in steel $< 750 \text{ N/mm}^2$	0.03 mm/rev.
Point angle	118 °
Nominal $\varnothing D_c$	0.7 mm
Overall length $L$	28 mm
Number of cutting edges $Z$	2
Shank	Plain shank
Series	CleverDrill
Coating	uncoated
Tool material	HSS
Type	N
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

## User data

	Suitability	$V_c$	ISO code
Alu plastics	suitable	80 m/min	N
Aluminium (short chipping)	suitable	60 m/min	N
Alu $> 10\% \text{ Si}$	suitable	50 m/min	N
Steel $< 500 \text{ N/mm}^2$	suitable	35 m/min	P
Steel $< 750 \text{ N/mm}^2$	suitable	32 m/min	P
Steel $< 900 \text{ N/mm}^2$	suitable	22 m/min	P
Steel $< 1100 \text{ N/mm}^2$	suitable	18 m/min	P
GG(G)	suitable	30 m/min	K
CuZn	suitable	40 m/min	N

Oil	suitable
wet maximum	suitable