

HEDI

Machine lamp DUO, Type: 6LEDWDUO



Order data

Order number	081306 6LEDWDUO
GTIN	
Item class	08B

Description

Version:

High-quality, universally usable lamp, with on/off switch and 3-m connection cable in black. Robust, long, coated flexible metal arm for good mobility of the lamp head and high stability. All Hedi® machine/workstation lamps come with table clamps, integrated magnet and 4 screws for flexible attachment of the lamp to a wide variety of surfaces as standard.

A fold-away lens allows the lamp to be quickly and easily switched over between spot and wide-beam illumination. Lamp head can be rotated and swivelled 340° using the ball joint. With exchangeable light source.

Nominal voltage: 250 V

Light colour: warm white bit

Colour temperature: 3000 K

Technical description

Nominal voltage	250 V
Colour temperature	3000 K
Type of fastening	Magnetic Base

Power supply	Mains operated
Light colour	warm white bit
Connection cable length	3 m
Bulb	LED
ATEX zone	no
Type of product	Machine lamp