

Garant
GARANT Master eco lever lock toolholder short, right-hand, Shank / insert size: 25/15mm

Order data

Order number	250624 25/15
GTIN	4062406728953
Item class	21U

Description
Version:

Highly efficient cooling directly on the cutter and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master eco toolholders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

ISO code toolholder	PDJNR/L 2525X15
Shim	259031 45
Overall length L	110 mm
Lever	259015 17
suitable indexable insert	DN.. 1506..
Functional width L ₄	32 mm
Head length L ₁	40 mm
Insert size	15 mm
Series	Master Eco
Lever screw	259018 17

Spring	259046 4
Shank size	25 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	yes
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar