

**Garant**
**GARANT Master eco lever lock toolholder short, right-hand, Shank / insert size: 25/08mm**

**Order data**

Order number	251910 25/08
GTIN	4062406734114
Item class	21U

**Description**
**Version:**

Highly efficient cooling directly on the cutter and additional flank face cooling.

**Note:**

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master eco toolholders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

**Technical description**

suitable indexable insert	WN.. 0804..
Series	Master Eco
Insert size	8 mm
Shim	259031 48
Shank size	25 mm
Head length L <sub>1</sub>	30 mm
Spring	259046 4
ISO code toolholder	PWLNRL 2525H08
Lever screw	259018 15

Functional width L <sub>4</sub>	32 mm
Overall length L	100 mm
Lever	259015 15
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	yes
Setting angle $\kappa$	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	QuickTurn clamping toolholder