

**Garant****DNMG 150608, Grade: HU7305-1**

## Order data

Order number	250762 HU7305-1
GTIN	4062406749828
Item class	21G

## Description

DNMG 150608 HU7305-1 Grade: HU7305-1  
Chip breaker: AM1  
Tolerance: M  
Cutting depth  $a_p$ : 0.2 - 5 mm  
Feed  $f$ : 0.05 - 0.6 mm/rev.  
Cutting speed  $v_c$  main application: 400 - 700 m/min

## Technical description

Cutting speed $v_c$ main application	400 - 700 m/min
Grade	HU7305-1
Corner radius	0.8 mm
Tool material	Carbide
Finishing/roughing assignment	Finishing
Chip breaker	AM1

Cutting depth $a_p$	0.2 - 5 mm
Coating	uncoated
Number of changes/inserts	4
Tolerance	M
ISO code indexable insert	DNMG 150608
Main application	N
Feed $f$	0.05 - 0.6 mm/rev.
Cutting conditions	slightly interrupted
Type of product	Indexable insert for turning