

Garant
VNMG 160408, Grade: HU7305-1


Order data

Order number	251804 HU7305-1
GTIN	4062406749866
Item class	21G

Description

VN.G 160408 HU7305-1 Grade: HU7305-1
 Chip breaker: AM1
 Tolerance: M
 Cutting depth a_p : 0.2 - 5 mm
 Feed f : 0.05 - 0.6 mm/rev.
 Cutting speed v_c main application: 400 - 700 m/min

Technical description

Cutting conditions	slightly interrupted
Main application	N
Feed f	0.05 - 0.6 mm/rev.
Cutting speed v_c main application	400 - 700 m/min
Number of changes/inserts	4
ISO code indexable insert	VNMG 160408

Tolerance	M
Cutting depth a_p	0.2 - 5 mm
Tool material	Carbide
Chip breaker	AM1
Grade	HU7305-1
Corner radius	0.8 mm
Finishing/roughing assignment	Finishing
Coating	uncoated
Type of product	Indexable insert for turning