

Garant
GARANT Master eco lever lock toolholder short, right-hand, Shank / insert size: 20/08mm

Order data

Order number	251910 20/08
GTIN	4062406733896
Item class	21U

Description
Version:

Highly efficient cooling directly on the cutter and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master eco toolholders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Lever screw	259018 15
Shank size	20 mm
Head length L ₁	30 mm
Lever	259015 15
ISO code toolholder	PWLNRL 2020X08
Shim	259031 48
Functional width L ₄	25 mm
Overall length L	90 mm
Spring	259046 4

Insert size	8 mm
suitable indexable insert	WN.. 0804..
Series	Master Eco
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	yes
Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	QuickTurn clamping toolholder