


Garant
TNMG 160408, Grade: HU7305-1


Order data

Order number	251544 HU7305-1
GTIN	4062406749842
Item class	21G

Description

TN.G 160408 HU7305-1 Grade: HU7305-1
 Chip breaker: AM1
 Tolerance: M
 Cutting depth a_p : 0.2 - 5 mm
 Feed f : 0.05 - 0.6 mm/rev.
 Cutting speed v_c main application: 400 - 700 m/min

Technical description

Chip breaker	AM1
ISO code indexable insert	TNMG 160408
Main application	N
Coating	uncoated
Feed f	0.05 - 0.6 mm/rev.
Grade	HU7305-1
Finishing/roughing assignment	Finishing

Cutting speed v_c main application	400 - 700 m/min
Tool material	Carbide
Cutting conditions	slightly interrupted
Tolerance	M
Corner radius	0.8 mm
Number of changes/inserts	6
Cutting depth a_p	0.2 - 5 mm
Type of product	Indexable insert for turning