


Garant
GARANT Master eco lever lock toolholder short, left-hand, Shank / insert size: 16/06mm

Order data

Order number	251911 16/06
GTIN	4062406734121
Item class	21U

Description
Version:

Highly efficient cooling directly on the cutter and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master eco toolholders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Lever screw	259018 16
suitable indexable insert	WN.. 0604..
Head length L ₁	30 mm
Spring	259046 5
Shank size	16 mm
Series	Master Eco
Overall length L	80 mm
Insert size	6 mm
ISO code toolholder	PWLNLR/L 1616F06

Functional width L ₄	20 mm
Shim	259031 47
Lever	259015 16
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	yes
Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar