

Garant**DNMG 150608, Grade: HB7130-2**

Order data

Order number	250762 HB7130-2
GTIN	4062406749965
Item class	21G

Description

DNMG 150608 HB7130-2 Grade: HB7130-2
Chip breaker: VM
Tolerance: M
Cutting depth a_p : 0.5 - 5 mm
Feed f : 0.2 - 0.5 mm/rev.
Cutting speed v_c main application: 70 - 240 m/min

Technical description

Corner radius	0.8 mm
Cutting depth a_p	0.5 - 5 mm
Tolerance	M
Tool material	Carbide
ISO code indexable insert	DNMG 150608
Finishing/roughing assignment	Finishing

Chip breaker	VM
Cutting speed v_c main application	70 - 240 m/min
Main application	M
Feed f	0.2 - 0.5 mm/rev.
Number of changes/inserts	4
Cutting conditions	slightly interrupted
Grade	HB7130-2
Type of product	Indexable insert for turning