

**Garant**
**Mechanical jointed measuring stand (without magnetic base), Throat: 240mm**

**Order data**

Order number	441610 240
GTIN	4062406729745
Item class	41D

**Description**
**Version:**

**Mechanic measuring stand with central clamping** – all joints are rigidly clamped by means of the central boring head. Clamping force can be steplessly adjusted. **Large rubberised handwheel** (Ø approx. 45 mm or approx. 55 mm) for easy tightening and releasing of the clamp. The dial indicator mounting on the jointed arm rotates 360°, can be twisted 180° and is suitable for dial indicators with shank Ø 6 and 8 mm or vee block. Connection thread for magnetic base M8, connection thread for jointed arm at the top M6.

**Optional extras:**

Holder for measuring stand No. 442100 and 442104.

**Technical description**

Length of jointed arm L <sub>1</sub>	110 mm
Connection thread	M8
Throat	240 mm
Length of jointed arm L <sub>2</sub>	101 mm

Type of product

measuring stand

---

**Accessories**Mechanical measuring stand (with magnetic base) Throat  
240 mm

441600 240