


Garant**WNMG 080408, Grade: HB7130-2**

Order data

Order number	252070 HB7130-2
GTIN	4062406750077
Item class	21G

Description

WN.G 080408 HB7130-2 Grade: HB7130-2
Chip breaker: VM
Tolerance: M
Cutting depth a_p : 0.5 - 4 mm
Feed f : 0.1 - 0.5 mm/rev.
Cutting speed v_c main application: 70 - 240 m/min

Technical description

Feed f	0.1 - 0.5 mm/rev.
Chip breaker	VM
Tool material	Carbide
Grade	HB7130-2
Cutting speed v_c main application	70 - 240 m/min
Corner radius	0.8 mm
ISO code indexable insert	WNMG 080408

Cutting depth a_p	0.5 - 4 mm
Tolerance	M
Cutting conditions	slightly interrupted
Number of changes/inserts	6
Main application	M
Finishing/roughing assignment	Finishing
Type of product	Indexable insert for turning