

**Garant**
**CC.T 060204, Grade: HB7130-2**


### Order data

Order number	260052 HB7130-2
GTIN	4062406750107
Item class	21G

### Description

CC.T 060204 HB7130-2 Grade: HB7130-2  
 Chip breaker: VS  
 Tolerance: M  
 Cutting depth  $a_p$ : 0.2 - 2.5 mm  
 Feed  $f$ : 0.1 - 0.3 mm/rev.  
 Cutting speed  $v_c$  main application: 80 - 270 m/min

### Technical description

Finishing/roughing assignment	Finishing
Cutting conditions	slightly interrupted
Feed $f$	0.1 - 0.3 mm/rev.
Tool material	Carbide
Corner radius	0.4 mm
Chip breaker	VS
Tolerance	M

Cutting speed $v_c$ main application	80 - 270 m/min
Number of changes/inserts	2
Cutting depth $a_p$	0.2 - 2.5 mm
ISO code indexable insert	CC.T 060202
Grade	HB7130-2
Main application	M
Type of product	Indexable insert for turning