


Garant**Eco clamping toolholder DDJNL 93°, for indexable inserts DN., left-hand****Order data**

Order number	250615 20/11
GTIN	4062406734824
Item class	21U

Description**Version:**

With internal coolant feed right to the cutting edge. Cooling by means of precision nozzles effectively and efficiently reduces the thermal loading, since the coolant stream is optimally directed between the chip and cutting edge. This results in higher productivity, longer tool life and increased process reliability.

Note:

Coolant transfer only possible in conjunction with GARANT eco system toolholders No. 319001 – 319886 or for shank length < 125 mm plus No. 317900.

Technical description

Series	Eco
Shim screw	259027 2
Head length L ₁	34 mm
Insert size	11 mm
Clamp, screw, spring	259036 11
Overall length L	97 mm
ISO code toolholder	DDJNR/L 2020X11
Functional width L ₄	25 mm
suitable indexable insert	DN.. 1104..

Data sheet

Shim	259033 3
Shank size	20 mm
Application type	left-hand
Through-coolant	yes
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/250615-20/11>