



Solid carbide milling cutter with chip separators TPC, TiAlN, Ø f8 DC: 10mm



Order data

| | |
|--------------|---------------|
| Order number | 203109 10 |
| GTIN | 4062406734954 |
| Item class | 12X |

Description

Version:

High-performance milling cutter with **irregular cutter spacing** and **irregular helical pitch**. Optimised bending strength due to the use of ultra-fine grain substrates. **Offset chip breakers for controlled chip breaking.**

Note:

h_{max} : The values stated in the table are maximum values. For finishing operations we recommend items No. 204012, 204014 and 204015.

$a_{e,max} = 0.07 \times D$ for TPC machining.

Technical description

| | |
|--|---------------|
| Corner chamfer width at 45° | 0.2 mm |
| Balance quality with shank | G 2.5 with HB |
| No. of teeth Z | 5 |
| Tolerance nominal Ø | e8 |
| Helix angle | 40 degrees |
| Overall length L | 80 mm |
| Corner chamfer angle | 45 degrees |
| Shank Ø D _s | 10 mm |
| Average chip thickness h_{max} for TPC milling in INOX < 900 N/mm ² | 0.051 mm |
| Flute length L _c | 30 mm |

| | |
|---|-------------------------|
| Cutting edge $\varnothing D_c$ | 10 mm |
| Shank | DIN 6535 HB to h6 |
| Recess $\varnothing D_1$ | 9.8 mm |
| Overhang length L_1 incl. recess | 35 mm |
| Direction of infeed | horizontal and oblique |
| Number of chip separators | 1 |
| Coating | TiAlN |
| Tool material | Solid carbide |
| Standard | Manufacturer's standard |
| Type | N |
| Helix angle characteristic | unequal spacing |
| Spacing of the cutters | unequal spacing |
| Cutting width a_e for milling operation | $0.07 \times D$ |
| Through-coolant | no |
| Machining strategy | TPC |
| Colour ring | blue |
| Type of product | End / face mill |

User data

| | Suitability | V_c | ISO code |
|--------------------------------|---|-----------|----------|
| Steel < 500 N/mm ² | suitable | 380 m/min | P |
| Steel < 750 N/mm ² | suitable | 340 m/min | P |
| Steel < 900 N/mm ² | suitable | 300 m/min | P |
| Steel < 1100 N/mm ² | suitable | 230 m/min | P |
| INOX < 900 N/mm ² | suitable | 240 m/min | M |
| INOX > 900 N/mm ² | suitable | 170 m/min | M |
| wet maximum | Suitable | | |
| wet minimum | Suitable only under restricted conditions | | |

Air

suitable