

Garant**DC.T 070202, Grade: HB7130-2**

Order data

Order number	260351 HB7130-2
GTIN	4062406750206
Item class	21G

Description

DCMT 070202 HB7130-2 Grade: HB7130-2
Chip breaker: VS
Tolerance: M
Cutting depth a_p : 0.2 - 1.5 mm
Feed f : 0.1 - 0.3 mm/rev.
Cutting speed v_c main application: 80 - 270 m/min

Technical description

Cutting depth a_p	0.2 - 1.5 mm
Cutting speed v_c main application	80 - 270 m/min
Tolerance	M
Grade	HB7130-2
Feed f	0.1 - 0.3 mm/rev.
Tool material	Carbide

Corner radius	0.2 mm
Cutting conditions	slightly interrupted
Number of changes/inserts	2
Finishing/roughing assignment	Finishing
ISO code indexable insert	DCMT 070202
Main application	M
Chip breaker	VS
Type of product	Indexable insert for turning