

Garant**CC.T 09T308, Grade: HB7130-2**

Order data

Order number	260152 HB7130-2
GTIN	4062406750176
Item class	21G

Description

CC.T 09T308 HB7130-2 Grade: HB7130-2
Chip breaker: VM
Tolerance: M
Cutting depth a_p : 0.2 - 4 mm
Feed f : 0.1 - 0.4 mm/rev.
Cutting speed v_c main application: 70 - 240 m/min

Technical description

Grade	HB7130-2
Feed f	0.1 - 0.4 mm/rev.
ISO code indexable insert	CCMT 09T308
Tool material	Carbide
Cutting depth a_p	0.2 - 4 mm
Corner radius	0.8 mm

Cutting conditions	slightly interrupted
Tolerance	M
Chip breaker	VM
Finishing/roughing assignment	Finishing
Main application	M
Number of changes/inserts	2
Cutting speed v_c main application	70 - 240 m/min
Type of product	Indexable insert for turning