

Garant**TC.T 110204, Grade: HB7130-2**

Order data

| | |
|--------------|-----------------|
| Order number | 260982 HB7130-2 |
| GTIN | 4062406750343 |
| Item class | 21G |

Description

TC.T 110204 HB7130-2 Grade: HB7130-2
Chip breaker: VM
Tolerance: M
Cutting depth a_p : 0.5 - 2.5 mm
Feed f : 0.1 - 0.4 mm/rev.
Cutting speed v_c main application: 70 - 240 m/min

Technical description

| | |
|---------------------------|----------------------|
| Cutting conditions | slightly interrupted |
| ISO code indexable insert | TCMT 110204 |
| Tool material | Carbide |
| Tolerance | M |
| Corner radius | 0.4 mm |
| Cutting depth a_p | 0.5 - 2.5 mm |
| Grade | HB7130-2 |
| Feed f | 0.1 - 0.4 mm/rev. |

| | |
|--------------------------------------|------------------------------|
| Chip breaker | VM |
| Number of changes/inserts | 3 |
| Cutting speed v_c main application | 70 - 240 m/min |
| Finishing/roughing assignment | Finishing |
| Main application | M |
| Type of product | Indexable insert for turning |