

**Garant**
**TCMT 16T308, Grade: HB7130-2**


### Order data

Order number	260988 HB7130-2
GTIN	4062406750367
Item class	21G

### Description

TCMT 16T308 HB7130-2 Grade: HB7130-2  
 Chip breaker: VM  
 Tolerance: M  
 Cutting depth  $a_p$ : 0.5 - 2.5 mm  
 Feed  $f$ : 0.1 - 0.4 mm/rev.  
 Cutting speed  $v_c$  main application: 70 - 240 m/min

### Technical description

Cutting conditions	slightly interrupted
Finishing/roughing assignment	Finishing
Cutting speed $v_c$ main application	70 - 240 m/min
Main application	M
ISO code indexable insert	TCMT 16T308
Grade	HB7130-2
Corner radius	0.8 mm
Cutting depth $a_p$	0.5 - 2.5 mm

Tolerance	M
Feed f	0.1 - 0.4 mm/rev.
Chip breaker	VM
Type of product	Indexable insert for turning